

## Cable - FLK 50/EZ-DR/ 50/KONFEK/S - 2299097


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 0.5 m



### Key commercial data

|                                      |  |
|--------------------------------------|--|
| Packing unit                         | 1 pc   |
| GTIN                                 | <br>4 017918 832230 |
| Weight per Piece (excluding packing) | 108.4 g  |
| Custom tariff number                 | 85444290   |
| Country of origin                    | Germany  |
| Note                                 | Made to Order (non-returnable)   |

### Technical data

#### General

|   |   |
|---|---|
| Nominal voltage $U_N$                         | < 50 V AC   |
|   | 60 V DC   |
| Max. current carrying capacity per path       | 1 A   |
| Max. conductor resistance                     | 0.16 $\Omega$ /m                                    |
| Length of cable                               | 0.5 m   |
| Single wire, cross section                    | 0.14 mm <sup>2</sup>                                |
| AWG   | 26  |
| Conductor construction: Number of litz wires: | 7   |
| Single wire, material                         | Cu tin-plated                                       |
| External diameter                             | 11 mm   |
| Cable, preassembly                            | Insulation displacement, IEC 60352-4/DIN EN 60352-4 |
| Shielding                                     | yes   |
|   | Tinned copper-braided shield, approx. 85% covering  |

#### Environmental conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
|---------------------------------|------------------|

## Cable - FLK 50/EZ-DR/ 50/KONFEK/S - 2299097

### Technical data

#### Environmental conditions

|   |                  |
|---|------------------|
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Flame resistance                        | IEC 60332-1      |

#### Connector, module side

|                     |                                |
|---------------------|--------------------------------|
| Number of positions | 50                             |
| Connectors          | IDC/FLK socket strip (2.54 mm) |
| Number of plugs     | 1                              |

#### Connector, controller side

|                     |                                |
|---------------------|--------------------------------|
| Number of positions | 50                             |
| Connectors          | IDC/FLK socket strip (2.54 mm) |
| Number of plugs     | 1                              |

#### Supported controller

|                     |                           |
|---------------------|---------------------------|
| Controller          | SIEMENS S7-300 / ET 200 M |
| - suitable I/O card | CPU 313C-2DP              |
|                     | CPU 314C-2PtP             |
|                     | 6ES7 321-1BL00-0AA0       |
|                     | 6ES7 322-1BL00-0AA0       |
|                     | 6ES7 323-1BL00-0AA0       |
|                     | 6ES7 331-7NF00-0AB0       |
|                     | 6ES7 331-7PF01-0AB0       |
|                     | 6ES7 331-7PF11-0AB0       |
|                     | 6ES7 350-2AH01-0AE0       |
|                     | 6ES7 357-4AH01-0AE0       |
|                     | CPU 314C-2DP              |
|                     | 6ES7 332-5HF00-0AB0       |
|                     | 6ES7 331-7NF10-0AB0       |
|                     | 6ES7 331-1KF01-0AB0       |
|                     | CPU 313C                  |
|                     | CPU 313C-2PtP             |
| Controller          | SIEMENS S7-400            |
| - suitable I/O card | 6ES7 421-1BL01-0AA0       |
|                     | 6ES7 421-7BH01-0AB0       |
|                     | 6ES7 421-7DH00-0AA0       |
|                     | 6ES7 422-1BL00-0AA0       |
|                     | 6ES7 422-7BL00-0AB0       |
|                     | 6ES7 431-0HH0-0AB0        |
|                     | 6ES7 431-1KF00-0AB0       |
|                     | 6ES7 431-1KF10-0AB0       |
|                     | 6ES7 431-1KF20-0AB0       |
|                     | 6ES7 431-7KF00-0AB0       |

## Cable - FLK 50/EZ-DR/ 50/KONFEK/S - 2299097

### Technical data

#### Supported controller

|                     |  |
|---------------------|--|
|                     | 6ES7 431-7KF10-0AB0                    |
|                     | 6ES7 431-7QH00-0AB0                    |
|                     | 6ES7 432-1HF00-0AB0                    |
| Controller          | Schneider Electric MODICON TSX QUANTUM |
| - suitable I/O card | DDI 353                                |
|                     | DDI 841                                |
|                     | DDI 853                                |
|                     | DAI 340                                |
|                     | DAI 353                                |
|                     | DAI 440                                |
|                     | DAI 453                                |
|                     | DDO 353                                |
|                     | DDM 390                                |
|                     | ACI 030                                |
|                     | ACI 040                                |
|                     | ATI 030                                |
|                     | ARI 030                                |
|                     | AVI 030                                |
|                     | ACO 020                                |
|                     | ACO 130                                |
|                     | AVO 020                                |
|                     | EHC 105                                |
|                     | EHC 202                                |
| Controller          | ALLEN-BRADLEY ControlLogix             |
| - suitable I/O card | 1756-IA16I                             |
|                     | 1756-IB16D                             |
|                     | 1756-IB16I                             |
|                     | 1756-IB32                              |
|                     | 1756-IH16I                             |
|                     | 1756-OB32                              |
|                     | 1756-IF8                               |
|                     | 1756-IF16                              |
|                     | 1756-HSC                               |
|                     | 1756-M02AE                             |
| Controller          | ALLEN-BRADLEY PLC 5                    |
| - suitable I/O card | 1771 IBN                               |
|                     | 1771 OBN                               |
| Controller          | HONEYWELL PlantScape                   |
| - suitable I/O card | TC-IDK 161                             |
|                     | TC-IDX 161                             |

## Cable - FLK 50/EZ-DR/ 50/KONFEK/S - 2299097

### Technical data

#### Supported controller

|                     |                       |
|---------------------|-----------------------|
|                     | TC-IDJ 161            |
|                     | TC-IDD 321            |
|                     | TC-ODD 321            |
|                     | TC-IAH 161            |
| Controller          | ALLEN-BRADLEY SLC 500 |
| - suitable I/O card | 1746 OA16             |
|                     | 1746 OW16             |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27249205 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11     | 26121620 |
| UNSPSC 12.01  | 26121620 |
| UNSPSC 13.2   | 26121620 |

### Approvals

#### Approvals

---

Approvals

EAC

---

Ex Approvals

## Cable - FLK 50/EZ-DR/ 50/KONFEK/S - 2299097

### Approvals

---

Approvals submitted

---

### Approval details

|     |
|-----|
| EAC |
|-----|

---