

Contact insert - HC-M-PN3-4,00-ST - 1663501


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Pneumatics pin, for HC-M-PN3 module, cross section of hose 4.0 mm



The illustration shows versions, pneumatic male, female and female with valve

Key commercial data

Packing unit	10 pc
GTIN	 4 017918 123314
Weight per Piece (excluding packing)	0.8 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical characteristics

Operating pressure, vacuum	8.00 bar
Internal diameter of pressure hose connection	4 mm
Insertion/withdrawal cycles	≥ 500

General

Color	black
-------	-------

Material data

Contact material	Delrin acetal
------------------	---------------

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424

Contact insert - HC-M-PN3-4,00-ST - 1663501

Classifications

eCl@ss

eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000796

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 
--