



Datasheet

Stock No: 811-4400

ENGLISH

**RS Pro BASEC 5 Core White
Unscreened 3185Y Stranded PVC
Power Cable H05VV-F, 0.75 mm² CSA 6
A 100m, 300/500 V**



Product Details

BASEC approved H05VV-F/3185Y 5 Core Cable

Flexible PVC Cable

Specifications:

Number of Cores	5
Cross Sectional Area	0.75 mm ²
Sheath Colour	White
Current Rating	6 A
Voltage Rating	300/500 V
Reel Length	100m
Outer Diameter	2.34mm
Sheath Material	Polyvinyl Chloride PVC
Harmonised Code	H05VV-F
Type	3185Y
Minimum Operating Temperature	-15°C
Screened/Unscreened	Unscreened
Conductor Strand Type	Stranded
Conductor Material	Copper
Core Strands	24/0.2 mm
Conductor Resistance	26 Ω/km
Number of Strands	24
American Wire Gauge	24 AWG
Size of Strands	0.2 mm
Length	100m
Insulation Material	PVC Type T11 to BS7655
Standards Met	BASEC