




Low profile transformer FL 14/9

Type		FL 14/9
Electrical data	Input	
	Rated input Voltage	2 x 115 Vac
	Rated frequency	50 - 60 Hz
	Output	
	Rated output voltage	2 x 9 Vac
	Rated Power	14.0 VA
	No-load voltage (app. x factor)	1.28
	No-load loss (typ.)	1.20 W
	Efficiency	74 %
	Standards	
Classification	Safety isolating transformer	
Approvals		
Approvals	cURus, ENEC 10 (VDE)	
Environment		
Ambient temperature max.	40 °C	
Safety and protection		
Type	encapsulated	
Class of Insulation System	VDE=E, UL=class 105	
Protection index	IP 00	
Safety class (prepared)	II	
Short circuit strength	non-short-circuit proof	
Order numbers		
Order Number	FL 14/9	

Type		FL 14/9
Terminal and mounting		
Terminals		Pins for printed circuit boards
Measures and weights		
Core type		UI 39/10,2
Weight		0.32 kg



Subjects to change.