







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DS			A	RELEASED	19.JUL'05	SC	JK



RECOMMENDED P.C.B LAYOUT

NOTES

- GENERAL TOLERANCES: $\pm 0.25, \pm 2^\circ$
- KEYING TYPE: SEE TABLE 1
- MATING PLUG HSG P/N: 1743419-□




TABLE 1 (SEE DETAIL J)

TYPE	A	B	C	D
KEYING LOCATION				

TABLE 2

ITEM	DESCRIPTION	MATERIAL
①	250 2P HDR HSG(11mm Pitch)	6/6 NYLON
②	TERMINAL FOR 250 2P HSG	BRASS

D	BLUE	1743330-6
C	YELLOW	1743330-4
B	RED	1743330-2
A	NATURAL	1743330-1
△TYPE	COLOR	ASS'Y P/N

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN: SC KIM		tyco Electronics AMP KOREA, kyungsan, korea	
DIMENSIONS: MM		CHK: BW KANG			
 3rd ANGLE PROJECTION		APVD: JK SONG		NAME	
		PRODUCT SPEC 108-61068		250 2P HDR ASS'Y (11mm Pitch)	
MATERIAL		FINISH		SIZE	
SEE TABLE 2		WEIGHT		CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
				A3 00779C= 1743330	
				SCALE 2/1 SHEET 1 OF 1 REV A	