



ENGLISH

## Datasheet

**RS 15 Core Unscreened Industrial Cable, PVC Sheath, 250 V, 4.5mm OD, 0.055 mm<sup>2</sup> CSA 0.25 A, 25m**

**Stock Number - 660-3999**



### Description:

**Rated Temperature (oC): -20 ~ 80**

**Rated Voltage (V):250**

**Flammability Test: IEC60332-1**



ENGLISH

**Construction:**

**Conductor:** Tinned Copper

**Conductor Dia. (mm):**  $0.10 \pm 0.008 \times 7$

**Insulation:** PVC

**Insulation Dia. (mm):**  $0.7 \pm 0.05 \times 15C$

**Tape:** Mylar Spiral

**Coverage:**  $\geq 115\%$

**ID Thread :** Green, White/Green

**A rip cord :** 210 D

**Jacket:** FR-PVC

**Outer Dia. (mm):**  $4.2 \pm 0.1$

**Colour:**

**The colour of the insulation:** Red , Blue

, Green , Yellow ,

White , Black , Brown , Violet , Orange ,

Pink , Light Green ,

Grey , Red/Blue , Green/Red ,

Yellow/Red

**The jacket colour:** Black

**Marking(3times/m):**

RS 6603999 7 - 1 – 15A

**Performance:****Electrical Characteristics:****Max.Conductor DC Resistance at 20°C (  $\Omega$ /Km ) :**

&lt;384

**Min.Insulation DC Resistance at 20°C (  $M\Omega$ \*KM ) :**

&gt;200

**Current Rating : 0.25 A**