

Specifications for BBP11 200 dpi UK Printer with CodeSoft

Application	Asset Identification; Barcode Labelling; Wire & Cable Marking
Article No.	361069
Colour Capability	Monocolour
Continuous vs Die Cut Labels	Continuous Tape & Die Cut Labels
Description	The Brady BBP™ 11 is a compact desk-top printer which provides high quality thermal transfer printing at a low cost. The Brady BBP™ 11 is an entry level thermal transfer printer for labels, tapes cable markers, sleeves and much more.
Order Reference	BBP11-24LUK + CS
PC Connectivity	Yes
Print Speed (mm/sec)	127
Print Technology	Thermal Transfer
Size - Depth (mm)	258.00
Size - Height (mm)	173.00
Size - Width (mm)	202.00
Smart Cell	No
Additional Information	8 hours of operation per day for 5 days
Stand Alone Printing	Yes
Total Qty per Pack	1 Piece(s) / Piece
Weight (kg)	2.5
Max. Label Width (mm)	118
Max. Liner Width (mm)	118
Max. Print Length (mm)	2286.00
Max. Print Width (mm)	106
Minimum Label Height (mm)	6

