





SPECIFICATION

MATERIALS:

HOUSING & INSERT: PBT

COUPLING: BRASS-NICKEL PLATED

O-RING: VITON

ELECTRICAL:

VOLTAGE: 10-30VDC

CURRENT RATING: 4A PER PORT, 12 AMPS MAX.

PROTECTION CLASS: IP68

NOTES:

THREADED PLUG FITTED TO PORTS 1 & 2 ONLY

PROTECTION CAP FITTED TO ALL M12 PORTS

FIXING HOLES TO SUIT M4 SCREWS

SAP-Nummer	alte Artikel-Nr.	Beschreibung	Farbe
SAP-NUMBER	OLD ENGINEERING-No.	DESCRIPTION	COLOR
1201190021	BKY803P-FBC	ULTRA LOCK MPIS 8 WAY-16 I/O -PUR	gelb/YELLOW

NEW RELEASE
EC NO: WEU2010-0220
DRWN:SBH
CHKD:
APPR:FPACHER

REV	DESCRIPTION
A	

QUALITY SYMBOLS	
▽=0	
◻=0	
GENERAL TOLERANCES (UNLESS SPECIFIED)	
	mm INCH
4 PLACES	± --- ± ---
3 PLACES	± --- ± ---
2 PLACES	± 0.05 ± ---
1 PLACE	± 0.10 ± ---
ANGULAR ± ---°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
SBH	2009/12/10
CHECKED BY	DATE
APOHL_WEU	2009/12/10
APPROVED BY	DATE
FPACHER	2009/12/17
MATERIAL NO.	
1201190021	
SIZE	
A3	

SCALE 1:1	DESIGN UNITS METRIC		THIRD ANGLE PROJECTION
TITLE ULTRA-LOCK MPIS 8 WAY-16 I/O -PUR			
 MOLEX INCORPORATED		SHEET NO. 1 OF 1	
DOCUMENT NO. SD-120119-022			
AINS INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			