

Talento LAN Plus



TALENTO LAN+

	Grässlin
Product Name	talento LAN plus
Description	Module for connecting the talento 892/992 plus to a LAN ethernet or internet network for program transfer
Dimensions H x W D (mm)	45 x 52,5 x 60
No. of Modules	3
Distributor cut-out (mm)	46 x 54
Connection voltage	230 V/50-60 Hz
Power consumption at 230 V AC	5 VA
Protection type	IP 20
Ambient temperature	0°C ... + 55°C
Protection class	II
Max. terminal capacity	4 mm ² captive +/- screw terminals
Sealable	yes
Programming	Remote programming by using talento dialog plus or via integrated web server
Remote access LAN/Ethernet	Yes
Remote access Internet	Yes
Remote operations	
reading out switching status	Yes
performing manual switching	Yes
checking time	Yes
timer alarms send by email (maintenance, power off....)	Yes
time synchronization via internet	Yes
Local signalization	
Power ON	Yes
Network connection	Yes
PLC synchronization	Yes