

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **31402-2110**
Status: **Active**
Overview: MX64™ Sealed Single Row Connectors
Description: 2.54mm MX64™ Sealed Single Row Crimp Housing, GET Terminal, Black, 2 Circuits, Mating Part: Keying A, with CPA Lock

Documents:

3D Model	Application Specification AS-31402-000 (PDF)
Drawing (PDF)	Test Summary TS-31402-001-1X2 (PDF)
Product Specification PS-31402-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	31402
Application	Power
More Detailed Tech Information	http://ewcap.uscarteams.org
Overview	MX64™ Sealed Single Row Connectors
Product Name	MX64™, USCAR
UPC	822348656622

Physical

Circuits (maximum)	2
Color - Resin	Black, Natural, Red
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy, Polyester
Net Weight	4.710/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	9A
-------------------------------	----

Material Info

Reference - Drawing Numbers

Application Specification	AS-31402-000
Product Specification	PS-31402-000
Sales Drawing	SD-31402-211
Test Summary	TS-31402-001-1X2



image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

31402Series

Mates With

Sensors, Other USCAR Interfaces

Use With

34230 Molex GET Terminals