

# PlugTail™ Industrial Extra Heavy-Duty Spec Grade Receptacles, 15A, 125V, Ivory

PT5262AI



PlugTail™ Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle 15amp 125volt Ivory



## features & benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: Ivory  
Product Series: PlugTail  
Type: Receptacles  
Duty: Heavy Duty

### Listing Agencies/Third Party Information

RoH S: No  
CUL Listing No: E140596  
cULus: Yes  
cUL Standard: UL498  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: E140596  
UL Listed: Yes  
UL Standard: UL498  
UN SPS C: 39121406

### **Dimensions**

Depth U S: .866"  
Height U S: 3.281"  
Width U S: 1.625"

### **Technical Information**

Amps: 15A  
NEMA Configuration Number: 5-15R  
NEMA Rating: Yes  
Volts: 125V  
Volts A C: 125  
Capacity: Duplex  
Grade Type: Industrial

### **Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant