


Capacitor, Ceramic, 0.47 uF, +/-10% Tol, 50 V, X8L



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	3.81	MAX
L	6.1	MAX
LL	25.4	MIN
F	0.51	+0.025/-0.076

Packaging Specifications	
Package Kind:	T&R
Package Size:	12in
Package Type:	Paper
Package Quantity:	2500

General Information	
Supplier:	KEMET
Application:	General Purpose
Sub Application:	AEC-Q200
Temperature Coefficient:	X8L
Body Type:	Axial Conformal
Lead Type:	Wire Leads
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications	
Capacitance:	0.47 uF
Voltage:	50 V
Tolerance:	+/-10%
Temperature Range:	-55/+150C
Dissipation Factor:	2.5%
Insulation Resistance:	2.1 GOhm