



Product information

Weller®

WXR 3

Code No. : **T0053500699**

Rework station

WXR 3 Power unit 230 V, 420 W

- All-in-one-Station
- Benchtop controller capability e.g. Zero Smog Systems
- Automatic tool recognition and power management
- Compatible with all WX tools
- Storage medium in hand piece
- Blue LED backlighting
- Multilingual menu navigation

Technical Data



This station is ESD safe.

Dimensions L x W x H:	273 x 235 x 102 mm (10,75 x 9,25 x 4,02 inch)
Weight:	ca. 6,7 kg
Mains supply voltage:	230 V, 50 Hz / 120 V, 60 Hz / 100 V 50/60 Hz
Power consumption:	420 W (600 W)
Safety class:	I, antistatic housing III, soldering tool

Fuse:	Overcurrent release 230 V; 2,0 A 120 V; 4,0 A
Temperature accuracy:	$\pm 9^{\circ}\text{C}$ ($\pm 17^{\circ}\text{F}$) depends on tool (WXHAP $\pm 30^{\circ}\text{C}$ / $\pm 80^{\circ}\text{F}$)
Temperature stability:	$\pm 2^{\circ}\text{C}$ ($\pm 4^{\circ}\text{F}$)
Equipotential bonding:	Via 3.5 mm pawl socket on back of unit
Display:	240 x 88 dots / Backlighting
USB-Schnittstelle:	The control unit comes with a USB port for installing firmware updates, configuration and monitoring.
Built in pump:	(Intermittent operation 30/30 s) Max. vacuum: 0,7 bar Max. flow: 18l/min Hot air max. 15 l/min
Additional vacuum pump:	Max. vacuum: 0,7 bar Max. flow: 18l/min