



ENGLISH

## RS Pro Manual Ball Valve Nickel Plated Brass 3/4 in BSPP

RS Stock No. 340-3244

Brand RS Pro



Image representative of range

## Product Details

### Ball Valve with Strainer

- Epoxy coated Aluminium Tee Handle
- 18//8 Stainless steel strainer with 0.65mm perforations
- Female ports both ends

### Ball Valves 1/4 Turn, WRC Approved, Tee Handle

Hot pressed, nickel plated brass full bore ball valves with Lever style operating handles. Suitable for oil, air, water, saturated steam or high temperature hot water services in domestic, commercial and industrial applications.

- Approved to WRC standards
- Red colour-coded 'Tee' handles
- Working Temperature Range (Fluid): -20 to +150°C

Add product to Compare

## Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/> Threaded Connection	3/4 in BSPP
<input type="checkbox"/> Attachment Type	Threaded
<input type="checkbox"/> Body Material	Nickel Plated Brass
<input type="checkbox"/> Thread Size	3/4in
<input type="checkbox"/> Safe for Use With	Air, Oil, Steam, Water
<input type="checkbox"/> Maximum Working Pressure	20 bar
<input type="checkbox"/> Handle Colour	Red
<input type="checkbox"/> Ball Material	Brass
<input type="checkbox"/> Thread Standard	BSPP
<input type="checkbox"/> Handle Material	Aluminium Alloy