


KEMET, Z-SMS, Ferrite Beads, Noise Suppression, 50 mOhms



Dimensions	
Chip Size	0603
L	1.6mm +/-0.15mm
W	0.8mm +/-0.15mm
T	0.8mm +/-0.15mm
B	0.3mm +/-0.2mm

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	4000

General Information	
Series:	Z-SMS
Style:	SMD Chip
Description:	Chip Bead Signal Line
Features:	Suppresses The XL Component; Helps Stop The Reduction Of The Wave-Form Integrity
RoHS:	Yes

Specifications	
Impedance:	22 Ohms (100 mHz)
Impedance Tolerance:	25%
Ripple Current:	1500 mA (MAX)
Temperature Range:	-55/+125°C
Resistance:	0.05 Ohms