

SPECIFICATIONS

Mechanical

Contact Carrier - Polyurethane (PUR)
Pin Contact - Copper Alloy
Socket Contact - Copper Alloy
Contact Plating - Gold over nickel
Molded Body - Polyurethane (PUR)
O-ring - Viton
Coupling nut - Nickel Plated Brass
Cable - 0.34mm² (#22AWG) black PUR jacket
Cable Conductors - 42 x 0.10mm Copper
Stranding, PVC insulation
Cable Ratings - 300V, -5C to 70C, Oil resistant cable
Cable Diameter - 0.197" (5.0mm)

Environmental

Protection - IP68, NEMA 6P
Ambient Operating Temperature - -20C to 90C

Electrical

Voltage Rating - 250V AC/DC
Amperage - 4A