



ENGLISH

Datasheet

RS Pro 22 Piece HSS Tap & Drill Set, M3 to M12

RS Stock No: **673-4702**



Product Details

RS Pro 22-piece tap and drill set includes M3 to M12 die taps and 2.5 to 10.2 mm tapping drills. These tools are made of HSS for added durability. The 7-piece drill set is fully ground with black finish. The tap and drill set is suitable for general workshop and engineering applications. It is supplied in a metal case with tap wrench.

Features and Benefits

- 14-piece HSS tap set containing taper and bottom tap of each size
- Tap sizes M3, M4, M5, M6, M8, M10, M12
- 7-piece HSS drill set fully ground with black finish
- Drill sizes 2.5, 3.3, 4.2, 5.0, 6.8, 8.5, 10.2 mm
- Taps manufactured to ISO standard
- Drills manufactured to DIN338
- Supplied in a metal case with tap wrench



Specifications:

Material	HSS
Maximum Drill Size	10.2 mm
Maximum Tap Size	M12
Minimum Drill Size	2.5 mm
Minimum Tap Size	M3
Number of Pieces	22



HSS Metric Drill Bits Set 19pcs, fully ground, black finish, DIN338

RS Stock Number	Manufacture Part No.	Size	Package
6734709	H1995	1-10x0.5mm	Round Plastic Drum

22 piece HSS Metric Tap and Drill Set

RS Stock Number	Manufacture Part No.	Package	Content
6734702	T9222	Metal box	14pcs HSS Taps: M3-M4-M5-M6-M8-M10-M12 7pcs Drills: 2.5-3.3-4.2-5.0-6.8-8.5-10.2mm 1pc No.1 1/2 tap Wrench

Arborless Carbide Holesaw

RS Stock Number	Manufacture Part No.	Size (mm)	Depth of Cut mm	Shank Dia. mm
6734706	S10700160	16	13	10
6734715	S10700190	19	13	10
6734718	S10700200	20	13	10
6734712	S10700220	22	13	10
6734721	S10700250	25	13	10
6734724	S10700320	32	13	10
6734728	S10700380	38	13	10
6734737	S10700400	40	13	10
6734730	S10700510	51	13	10

HSS Conduit Holesaw

RS Stock Number	Manufacture Part No.	Size (mm)	Depth of Cut mm	Shank Dia. mm
6734743	S10600200	20	8	10
6734746	S10600250	25	8	10

Pilot Drills

RS Stock Number	Manufacture Part No.	Dia. (mm)	Overall Length mm	Application
6734734	S10700650	6.0	50	for Carbide Holesaw
6734740	S10600563	3/16"	65	for HSS holesaw