

Cable protection end sleeve - WP-SC BRASS WP PVC 27 - 3241076

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




End sleeves as cable protection, made of brass, for WP-STEEL PVC C

Image shows WP-TS BRASS 14 version



Key commercial data

Packing unit	25 pc
Minimum order quantity	25 pc
GTIN	 4 046356 712194
Weight per Piece (excluding packing)	10.09 g
Custom tariff number	74122000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Diameter	27.00 mm
----------	----------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 250 °C
---------------------------------	-------------------

General

Color	Brass
Components	Halogen-free
Material	Brass

Classifications

eCl@ss

eCl@ss 4.0	27141209
------------	----------

Cable protection end sleeve - WP-SC BRASS WP PVC 27 - 3241076

Classifications

eCl@ss

eCl@ss 4.1	27141209
eCl@ss 5.0	21132007
eCl@ss 5.1	21132007
eCl@ss 6.0	21132007
eCl@ss 7.0	27439210

ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC000519

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Accessories

Accessories

Corrugated pipe

Protective hose - WP-STEEL PVC C 27 - 3240871



Galvanized steel protective hose with PVC coating, 1 Pcs. / Pkt. = roll à 10 m