

Female test connector - PSBJ 4/15/6 WH - 0303312

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Female test connector, Color: white

Why buy this product

- The test socket PSBJ... is used in place of the normal bridge screw and ensures the voltage pick-off on a bridged group of terminals
- The test sockets are tailored to the special applications encountered in the power supply industry



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 000424
Weight per Piece (excluding packing)	3.26 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Length	6 mm
Width	6 mm

General

Color	white
Minimum temperature	-40 °C
Maximum temperature	80 °C

Classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127

Female test connector - PSBJ 4/15/6 WH - 0303312

Classifications

eCl@ss

eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002555

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

Female test connector - PSBJ 4/15/6 WH - 0303312

Dimensioned drawing

