


FILE NO:

DESCRIPTION CONTROL

REV	DESC	DATE	ECN NO
-----	------	------	--------



RoHS COMPLIANT



* 220030000361	TIE-A-BE	120*1	MM						
* 310000000011	CARTON:46*30*20CM	A/R	PCS						
* 300010000001	PE BAG:30*28*0.08MM	A/R	PCS						
* 300030000017	PE BAG:8*10*0.06MM	1	PCS	*		LABEL:7587548*45*25MM(條碼貼紙)<黃底黑字>			1 PCS
10 100500128003	JUMP-WIRE-28#-BLACK-UL1007	25*9	MM	INNER MOLDING	IDB9-1507	IDB2514			
9 240010100040	SRW-E32.5/BE02	4	PCS	OUTER MOLDING	IDB9-1505	IDB2512			
8 240010100034	SRW-E31.5/BE02	4	PCS						
7 120010000006	PVC-BE02/50	102.6	G						
6 120020000001	PE-5321	17	G						
5 230020000014	SOL-WIRE-FULL TIN-1.0	0.8	G						
4 100-0920120010-C	CDS-09F<BLACK>	2	PCS						
3 100-2520120010-C	CDS-25F<BLACK>	2	PCS						
2 12017065020083	NON-UL 28AWG 6C+AD BE02 OD:4.5MM	0.64/2*2	M						
1 12017065020083	NON-UL 28AWG 6C+AD BE02 OD:4.5MM	1.83	M						
NO	PART NO	DESCRIPTION		QTY	UNIT	ALL DIMENSIONS IN mm (UNLESS OTHERWISE SPECIFIED)			

PIN ASSIGNMENT			
P1	P2	P3	P4
3—2—3—2			
2—3—2—3			
1+6+8—5+6+8—20—7			
5—7—7—5			
7—20—5+6+8—1+6+8			
1+6+8—8—20—7			
S—S—S—S			

* 7587548	1	PCS							
RoHS	7587548	1	PCS						
Made in China									
xx/xx									

RoHS COMPLIANT									
----------------	--	--	--	--	--	--	--	--	--

ITEM: 7587548	REV: A
---------------	--------

DRAWN BY: 向三茶	SCALE: NONE	DATE: 2011.06.14
CHECKED BY:	CUSTOMER: C331 RS	PAGE: 1/1
APPROVED BY:	CUSTOMER P/N: 7587548	