

Product Information

ETX085x105-Ø20 NL110-Type E

EAN 4031582332049

Wheel centre made of steel, tread made of Polyurethane, casted, precision ball bearing, sealed

Wheel diameter	85 mm
Width of Tread	105 mm
Axle Hole Ø	20 mm
Hub length	110 mm
Temperature	- 20 / + 60 °C
Dynamic Load capacity	1000 kg
Static Load capacity	2000 kg
Hardness of tread	A 92 Shore

