



Main

Range	TeSys
Device short name	LA1LC
Product or component type	Auxiliary contact

Complementary

Range compatibility	TeSys Integral contactor breaker
Mounting location	Right side
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NO + 1 NC for contactor state 1 C/O for control knob in any position other than auto 1 C/O for tripped 1 C/O for tripped on short-circuit
[Ui] rated insulation voltage	690 V
[Ith] conventional free air thermal current	6 A
Connections - terminals	Screw clamp terminals 2 cable 1.5 mm ² Screw clamp terminals 1 cable 2.5 mm ²
Product weight	0.28 kg

Environment

Environmental characteristic	Standard environment
------------------------------	----------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------