



ENGLISH

Datasheet

## RS Pro PET D-sub Connector Backshell, 25 Way

RS Stock No: **544-4382**



### Product Details

RS Pro screwdown cover with jackscrews has 25 number of contact with B D-sub shell size in a PET housing. This straight screwdown cover is suitable for use with most standard and crimp D-connectors. This provides locking action with jack screws in combination with female screwlock assembly. The cover allows you for side or top cable entry through removable knockouts and cable retention.

### Features and Benefits

- Cable to panel adapter system suitable for use with most standard and crimp D connectors
- Cover in black moulded Noryl to UL94V-0
- Offers locking action with jack screws in combination with female screwlock assembly
- Side or top cable entry via removable knockouts and cable retention
- Temperature of -20 to +75°C



ENGLISH

### Specifications:

Body Orientation	Straight
Colour	Black
Housing Material	PET
Number of Contacts	25
Dimensions	48 x 56.6 x 16.3 mm
Operating Temperature Range	-20 to +75°C
Standards Met	UL 94V-0