



Sample photo

**Order symbol:** AL 082506  
**Product nbr:** 7011190  
**Description:** Enclosure  
**Remarks:** Aluminium

**EAN:** 6418074004147  
**EI. number:**  
 Finland 3423615  
 Denmark 8212004676  
 Italy 7321045  
 Sweden 2536317

**Including:** Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:			Rating:	
	L	W	H	
mm:	81	252	57	<b>Ingress Protection (EN 60529):</b> IP 66/67
inch:	3.2	9.9	2.2	<b>Impact Resistance (EN 50102):</b> IK 08
Materials:			<b>NEMA Class:</b> NEMA 1, 4, 4X, 12, 13	
<b>Material:</b>	AL		Certificates:	
<b>Base colour:</b>	RAL 7001		Underwriters Laboratories	
<b>Cover colour:</b>	RAL 7001		UL Canada	
<b>Cover screws material:</b>	Stainless steel			
<b>Gasket material:</b>	Polyurethane			
Temperatures:				
<b>Short term:</b>	-50 ... 140 °C			
<b>Continuous:</b>	-50 ... 80 °C			
<b>Short term:</b>	-60 ... 285 °F			
<b>Continuous:</b>	-60 ... 175 °F			
Accessories:				
AM 0808	Mounting plate			
AM 0813	Mounting plate			
AM 0818	Mounting plate			
AM 0825	Mounting plate			
ARM 0808	DIN-15 Mounting rail			
ARM 0825	DIN-15 Mounting rail			
ARH 26	DIN-35 Mounting rail			
MR 75003	Taptite screw			
MRS 28540	Wall fastening lug set			

