



ENGLISH

Datasheet

Stock No: 798-460

RS Pro Draining Tap Threaded Fitting



Product Details

Brass Draining Taps

- Gunmetal body and plug
- Brass gland, hose union and security cap
- Graphite, non-asbestos, gland seal
- Manufactured to BS2879-2
- Taper thread and plain shank types available
- BSP Taper Thread complies with BS21
- Hydraulically tested to 20 bar
- Maximum working pressure 10 bar at 120°C
- Incorporates ethylene propylene 'O' ring seal, preventing water loss via spindle

Specifications:

Fitting Type

Draining Tap