



fitted with

work equipment
connected load
power consumption
system of protection
class of protection
technology
usage
luminaire body
lamp cover
tubular sections
weight (net)
mains lead

fastening

lens; dimensions
lens; diopters
add-on lens; dimensions

63 x Light-emitting diode
light colour neutral white, 3700-4300 K, Color Rendering Index (CRI)=80-89
Energy efficiency category A+
electronic plug-in transformer
100-240 V; 50/60 Hz
approx. 6 W
IP 20
II
switchable
Touch-LED
aluminium/plastic, anodised, black
acrylic clear
steel tube/metal flexible tube, painted, silver metallic
approx. 1.1 kg
approx. 2.3 m; mains plug
CEE 7/XVI
NEMA 1-15P
screw-down flange, magnetic base (accessory), table clamp (accessory), wall bracket (accessory)
Ø 72 mm
6
not available



CEE 7/XVI



NEMA 1-15P

illuminance

measuring conditions: d=15cm

Em: 2663 lx
Emax: 5282 lx
Emin: 813 lx

