



Sample photo

**Order symbol:** AL 234011  
**Product nbr:** 7011400  
**Description:** Enclosure  
**Remarks:** Aluminium

**EAN:** 6418074004277  
**El. number:**  
Finland: 3423641  
Denmark: 8212004838  
Italy: 7321110

Including: Base with screws for mounting plate/DIN-rail, cover with neoprene gasket and stainless steel cover screws.

| Dimensions:                   |                            | Length | Width | Height | Rating:   |
|-------------------------------|----------------------------|--------|-------|--------|---|
| <b>mm:</b>                    |                            | 401    | 230   | 110    | Ingress Protection (EN 60529): IP 66/67   |
| <b>inch:</b>                  |                            | 15.8   | 9.1   | 4.3    | Impact Resistance (EN 62262): IK 08   |
| <b>Materials:</b>             |                            |        |       |        | NEMA Class: NEMA 1, 4, 4X, 12, 13   |
| <b>Material:</b>              | Aluminium                  |        |       |        | <b>Certificates:</b><br>Underwriters Laboratories<br>Fimko<br>UL Canada<br>Gost R |
| <b>Base colour:</b>           | RAL 7001                   |        |       |        |   |
| <b>Cover colour:</b>          | RAL 7001                   |        |       |        |   |
| <b>Cover screws material:</b> | Stainless steel            |        |       |        |   |
| <b>Gasket material:</b>       | Neoprene                   |        |       |        |   |
| <b>Temperatures:</b>          |                            |        |       |        |   |
| <b>Short term:</b>            | -50 ... 140 °C             |        |       |        |   |
| <b>Continuous:</b>            | -50 ... 80 °C              |        |       |        |   |
| <b>Short term:</b>            | -60 ... 285 °F             |        |       |        |   |
| <b>Continuous:</b>            | -60 ... 175 °F             |        |       |        |   |
| <b>Accessories:</b>           |                            |        |       |        |   |
| AM 2340                       | Mounting plate             |        |       |        |   |
| ARH 40                        | DIN-35 Mounting rail       |        |       |        |   |
| MRS 28541                     | Wall fastening lug (2 pcs) |        |       |        |   |
| PH A & AH A/B                 | Hinge set                  |        |       |        |   |

