

Input module - UM-2KS50/16DI/RS/MKDS - 2900173


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



16-channel digital input module with screw connection and redundant voltage supply. Suitable for Yokogawa SDV 144 card.



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 484053
Weight per Piece (excluding packing)	474.0 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	162 mm
Height	112 mm
Depth	80 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
---------------------------------	------------------

General

Note	Voltage monitoring on the module does not work in combination with upstream HESILED fuse terminal blocks with integrated LED display.
Max. permissible operating voltage	24 V DC ±5 %
Max. perm. current (per branch)	100 mA
Max. permissible current (separate power supply)	2 A (F150, F151) plug-in fuse (5x20, 2 A), DIN 41662
Number of positions	50
Status display	Green LED (supply), yellow LED (channel)
Mounting position	any

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Technical data

General

Designation	Air and creepage distances
Standards/regulations	DIN EN 50178
Rated surge voltage	basic insulation
Pollution degree	2
Surge voltage category	III

Connection data for connection 1

Connection name	Field level
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14

Connection data for connection 2

Connection name	Controller level
Number of connections	2
Connection method	Yokogawa KS-compatible
Number of positions	50

Supported controller

Controller	YOKOGAWA ProSafe-RS
- suitable I/O card	SDV144

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27242608

ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001437
ETIM 5.0	EC001437

UNSPSC

UNSPSC 6.01	30211824
-------------	----------

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Classifications

UNSPSC

UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

CSA

Ex Approvals

Approvals submitted

Approval details

CSA

Accessories

Accessories

System cable

Cable - FLK 50-PA/EZ-DR/KS/ 100/YUC - 2900991



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 1.0 m.

Cable - FLK 50-PA/EZ-DR/KS/ 200/YUC - 2314299



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 2.0 m

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Accessories

Cable - FLK 50-PA/EZ-DR/KS/ 300/YUC - 2314309



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 3.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 400/YUC - 2314312



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 4.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 500/YUC - 2321499



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 5.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 600/YUC - 2314927



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 6.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 700/YUC - 2321509



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 7.0 m

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Accessories

Cable - FLK 50-PA/EZ-DR/KS/ 800/YUC - 2314930



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 8.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 900/YUC - 2321512



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 9.0 m

Cable - FLK 50-PA/EZ-DR/KS/1000/YUC - 2314325



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 10.0 m

Cable - FLK 50-PA/EZ-DR/KS/1100/YUC - 2321389



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 11.0 m

Cable - FLK 50-PA/EZ-DR/KS/1200/YUC - 2321525



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 12.0 m

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Accessories

Cable - FLK 50-PA/EZ-DR/KS/1300/YUC - 2321392



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 13.0 m

Cable - FLK 50-PA/EZ-DR/KS/1400/YUC - 2321402



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 14.0 m

Cable - FLK 50-PA/EZ-DR/KS/1500/YUC - 2314338



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 15.0 m

Cable - FLK 50-PA/EZ-DR/KS/1600/YUC - 2321538



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 16.0 m

Cable - FLK 50-PA/EZ-DR/KS/1700/YUC - 2321541



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 17.0 m

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Accessories

Cable - FLK 50-PA/EZ-DR/KS/1800/YUC - 2321554



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 18.0 m

Cable - FLK 50-PA/EZ-DR/KS/1900/YUC - 2321567



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 19.0 m

Cable - FLK 50-PA/EZ-DR/KS/2000/YUC - 2314503



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 20.0 m

Cable - FLK 50-PA/EZ-DR/KS/2500/YUC - 2314516



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 25.0 m

Cable - FLK 50-PA/EZ-DR/KS/3000/YUC - 2314529



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 30.0 m

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Accessories

Cable - FLK 50-PA/EZ-DR/KS/5000/YUC - 2318981



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 50.0 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 100/YUC - 2904739



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 1 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 200/YUC - 2904740



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 2 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 300/YUC - 2904741



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 3 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 400/YUC - 2904742



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 4 m

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/ 500/YUC - 2904636



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 5 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 600/YUC - 2904743



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 60 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 700/YUC - 2904744



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 7 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 800/YUC - 2904745



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 8 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 900/YUC - 2904746



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 9 m

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/1000/YUC - 2904637



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 10 m

Cable - FLK 50-PA/EZ-DR/HF/KS/1500/YUC - 2904638



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 15 m

Cable - FLK 50-PA/EZ-DR/HF/KS/2000/YUC - 2904487



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 20 m

Cable - FLK 50-PA/EZ-DR/HF/KS/2500/YUC - 2904639



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 25 m

Cable - FLK 50-PA/EZ-DR/HF/KS/3000/YUC - 2904640



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 30 m

Input module - UM-2KS50/16DI/RS/MKDS - 2900173

Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/3500/YUC - 2904641



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 35 m

Cable - FLK 50-PA/EZ-DR/HF/KS/4000/YUC - 2904642



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 40 m

Cable - FLK 50-PA/EZ-DR/HF/KS/4500/YUC - 2904643



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 45 m

Cable - FLK 50-PA/EZ-DR/HF/KS/5000/YUC - 2904644



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 50 m
