


# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

<b>Brand</b>	C.K
<b>Product Range</b>	Pocket balances
<b>Catalogue number</b>	6202
<b>Date</b>	20/02/2009

<p><b>Range Description</b> Pocket balances</p> <p><b>Features</b></p> <p><b>4366</b></p> <ul style="list-style-type: none"> <li>• Calibrated in 1lb &amp; 0.5Kg divisions</li> <li>• Brass scale, black lacquered case and tinned hook and ring for corrosion resistance</li> </ul>	 <p>6202</p>
--	--

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T6202 025	Pocket Balance 12.5Kg/25lb	5013969629507	84238190	12
T6202 032	Pocket Balance 15Kg/32lb	5013969629606	84238190	12
T6202 044	Pocket Balance 20Kg/44lb	5013969629705	84238190	12
T6202 050	Pocket Balance 23Kg/50lb	5013969629804	84238190	6
T6202 066	Pocket Balance 30Kg/66lb	5013969629903	84238190	6
T6202 088	Pocket Balance 40Kg/88lb	5013969630008	84238190	6
T6202 112	Pocket Balance 50Kg/112lb	5013969630107	84238190	6

Technical product information	<b>Weight capacities</b> <table border="1"> <thead> <tr> <th rowspan="2">Item</th> <th colspan="2">Scale</th> </tr> <tr> <th>KG</th> <th>Lbs</th> </tr> </thead> <tbody> <tr> <td>T6202 025</td> <td>12.5</td> <td>25</td> </tr> <tr> <td>T6202 032</td> <td>15</td> <td>32</td> </tr> <tr> <td>T6202 044</td> <td>20</td> <td>44</td> </tr> <tr> <td>T6202 050</td> <td>23</td> <td>50</td> </tr> <tr> <td>T6202 066</td> <td>30</td> <td>66</td> </tr> <tr> <td>T6202 088</td> <td>40</td> <td>88</td> </tr> <tr> <td>T6202 112</td> <td>50</td> <td>112</td> </tr> </tbody> </table>	Item	Scale		KG	Lbs	T6202 025	12.5	25	T6202 032	15	32	T6202 044	20	44	T6202 050	23	50	T6202 066	30	66	T6202 088	40	88	T6202 112	50	112
Item	Scale																										
	KG	Lbs																									
T6202 025	12.5	25																									
T6202 032	15	32																									
T6202 044	20	44																									
T6202 050	23	50																									
T6202 066	30	66																									
T6202 088	40	88																									
T6202 112	50	112																									
Standards compliance	None applicable																										
User health and safety information	None applicable																										
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations																										
Material safety data	None applicable																										
Warranty	C.K Products are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered																										
Country of origin	Taiwan																										

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T6202 025	30	16	180	66	-	-	-	-
T6202 032	30	20	230	90	-	-	-	-
T6202 044	30	20	230	106	-	-	-	-
T6202 050	40	25	250	178	-	-	-	-
T6202 066	40	20	250	168	-	-	-	-
T6202 088	50	25	350	310	-	-	-	-
T6202 112	50	25	350	310	-	-	-	-

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T6202 025	110	112	160	845		
T6202 032	120	170	60	1140		
T6202 044	120	170	60	1320		
T6202 050	120	170	60	1105		
T6202 066	120	170	60	1065		
T6202 088	140	260	60	1980		
T6202 112	140	260	60	1955		

### Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T6202 025							53	Box
T6202 032							60	Box
T6202 044							60	Box
T6202 050							60	Box
T6202 066							60	Box
T6202 088							80	Box
T6202 112							80	Box