

# WINSLOW ADAPTICs

## Data Sheet – Stamped SIMM Socket WS3130SMRRC

The WS3130SMRRC Series features a metal latch and uses a phosphor bronze contact plated in 6 microns pure tin over 2.5 microns nickel. Moulding material is Liquid Crystal Polymer rated to UL 94 V-0.



### Performance Specifications

Current Rating: 1 Amp. Max.  
Operating Temperature: -55°C to +105°C  
Insulation Resistance: 10,000 MOhms Min. Initial.  
Durability: 40 cycles minimum.  
RoHS Compliant.

