

# HUBER+SUHNER® DATA SHEET

## Coaxial PCB Connector: 82\_MMBX-S50-0-3/111\_N

Rev.: G



### Description

Straight PCB jack

Interface Standards  
SUHNER-MMBX



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 12.4 GHz

#### Mechanical Data

Board mounting type surface mount  
Weight 0.0006 kg

#### Environmental Data

Operating Temperature -55 °C to 155 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts

Centre contact  
Outer contact  
Body  
Insulator

##### Material

Brass  
Brass  
Brass  
LCP

##### Surface Plating

SUCOPRO Plating  
SUCOPRO Plating  
SUCOPRO Plating

### Related Documents

Outline drawing DOU-00012608  
Catalogue drawing DCA-00012610  
Mounting hole DOU-00012611

### Ordering Information

Tape and Reel package 82\_MMBX-S50-0-3/111\_NM  
Bulk 100 pcs package 82\_MMBX-S50-0-3/111\_NH  
Single package 82\_MMBX-S50-0-3/111\_NE  
Tape and Reel package 82\_MMBX-S50-0-3/111\_NM-1

### Remarks

PCB connector with stand-offs

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**