



ENGLISH

RS Pro PUR Green Flexible Tube 60m Long Reinforced

RS Stock No. 351-3127

Brand RS Pro



Image representative of range

Product Details

P.U. Hose (Food Quality)

A four layer reinforced hose, made from anti-abrasive P.U. and thermoplastic rubber compound

Highly flexible, small bend radius

High resistance to ozone, hydrocarbons, fats, oils, and aggressive chemical products

Applications include pneumatic tooling, spray and paint guns, sandblasting and general airline

Article	Inner Dia.	Outer Dia.	Total Thickness	Weight	Bending Radius	Working Pressure 1:3 23°C	Working Pressure 40°C	Working Pressure 60°C	Bursting Pressure 23°C	Coil Length
3513048	1/4 in, 6mm	10mm	2mm	70g/m	20mm	20 bar	17 bar	15 bar	60 bar	100m
3513127	5/16 in, 8mm	12mm	2mm	85g/m	22mm	20 bar	17 bar	15 bar	60 bar	60m
3513133	3/8 in, 10mm	15mm	2.5mm	130g/m	38mm	20 bar	17 bar	15 bar	60 bar	50m
3513155	1/2 in, 13mm	19mm	3mm	195g/m	65mm	20 bar	17 bar	15 bar	60 bar	30m

Note

This data refers to performance at 18°C. Any changes in temperature will affect the performance data



Polyurethane Hose

Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/> Inner Diameter	8mm
<input type="checkbox"/> Outer Diameter	12mm
<input type="checkbox"/> Material	PUR
<input type="checkbox"/> Colour	Green
<input type="checkbox"/> Reinforced	Yes
<input type="checkbox"/> Suitable Applications	Compressed Air, Water
<input type="checkbox"/> Length	60m
<input type="checkbox"/> Minimum Operating Temperature	-15°C
<input type="checkbox"/> Maximum Operating Temperature	+60°C
<input type="checkbox"/> Maximum Working Pressure	20 bar
<input type="checkbox"/> Operating Temperature Range	-15 to +60 °C