

ITT 350 W 235 V-0170 R7S

HALOTHERM | Infrared halogen lamps, quartz clear



Areas of application

- Plastics, paper and printing industries
- Drying paint and varnishes
- Coil coating
- Keeping food warm in restaurants

Product benefits

- Short response time
- High efficiency
- Precise controllability
- Long lamp life



Product datasheet

Technical data


Electrical data

Nominal wattage	350.00 W
Nominal voltage	235 V
Nominal current	1.5 A
Lamp current	1.50000 A
Construction voltage	235 V

Photometrical data

Color temperature	2350 K
-------------------	--------

Dimensions & weight



Diameter	10.0 mm
Length	185.7 mm
Filament length	120.00 mm

Lifespan

Lifespan	5000 h
----------	--------

Additional product data

Base (standard designation)	R7s
-----------------------------	-----

Capabilities

Burning position	p15
Fuse, quick-acting	4.0 A

Country specific information

Product code	METEL code	SEG-No.	STK number	UK Org
--------------	------------	---------	------------	--------

Product datasheet

4008321204219	OSRHALOTT350	-	4739783	-
---------------	--------------	---	---------	---

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321204219	ITT 350 W 235 V- 0170 R7S	Folding carton box 1	26 mm x 26 mm x 238 mm	0.16 dm ³	33.00 g
4008321204226	ITT 350 W 235 V- 0170 R7S	Shipping carton box 12	117 mm x 95 mm x 250 mm	2.78 dm ³	352.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.