

CabinetMate Plug-In Outlet Center Unit / 120V/20A/20" long/8 O/L /6' cord

2008ULBC20R



Eight 20A outlets with t-slots, 6' [1.8m] cord. Length 20" [508mm]. Receptacle center-to-center 1 1/4" [32mm]. 2- Amp unit with a 20A resettable circuit breaker.

features & benefits



specifications

Technical Information

Amps: 20
Mounting: 0U
Rated Voltage: 120V
Number Of Circuits: 1
Receptacle Type: NEMA
Network Monitoring: No
Surge Suppression: Computer Grade
Number Of Outlets: 8

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant