

LIGHTS

3660

Little ED Rechargeable
Recoil LED Zone 1

Save as PDF



Peli lights - LED technology rechargeable lights

The rechargeable version of the The Little Ed 3660 LED uses a long-life NiMH battery pack for extended burn time. It comes with a charger base unit that can be installed at home or work using the 220V transformer, or in a vehicle through direct wiring or 12V plug-in adapter. Certified to ATEX Zone 1 (Category 2).



Peli lights - LED technology rechargeable lights
ANSI FL1 Specifications

Materials

Body	Lens	Shroud	Switch Type
Anti-	Polycarbonate	ABS	One-handed

	High	
LIGHT SOURCE.	LED	
BATTERIES	4 AA Ni-MH (Included)	
CHARGE TIME	NiMH Battery Pack 2-3 hours	
VOLTAGE	4.8	
LENGTH	19.1 cm (7.51")	
WEIGHT W/ BATTERIES	0.14 kg (4.8 oz.)	
WEIGHT W/O BATTERIES	0.2 kg (6.9 oz.)	






LIGHT OUTPUT

RUNTIME (hours/min)


BEAM DISTANCE (meters)

PEAK BEAM INTENSITY (candela)

WATER RESISTANT

FL1 STANDARD	High	
		
	4h 30m	
	153m	
	5828cd	
		

Approvals

CE  - II 2 G Ex ib IIC T4 Gb
 Certificate: EPSILON 07ATEX2168X

static ABS		safety switch operation
------------	--	-------------------------

Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
Stainless Steel	Stainless Steel; Phosphore Bronze and Brass Nickel Plate	Ethylene Propylene	N/A

Configuration

Cat. #	Description
--------	-------------

Peli lights - LED technology rechargeable lights Accessories

Cat. #	Description
2468	220V Transformer
2469	NiMH Replacement Battery Pack
8056F	12V Plug-in for Fast Charger
6061F	Direct Wiring Rig for Fast Charger
2458	220V Adapter NiMH