



Datasheet

ENGLISH

RS Pro USB Microscope, 1280 x 1024 pixel, USB 2.0, x10 → 230

Stock No: 800-3072



Contents:

- Adjustable focus (10-100x, 230x)
- High precision lens
- 8 built in adjustable led for illumination
- Instant snapshots and time lapse video
- With tripod stand
- With measurement soft ware AP

Features:

- Recording in pc interface: USB2.0
- Max active pixels: 1.3m(1280x 1024)
- Optical format: 1/4"
- White balance: Automatic
- Recording frame rate: SX GS 15/VGA 30
- Transmission range : Cable dependant
- Max zoom time: 282x Feature:
- High resolution: 1.3 mega pixel sensor the Chrono's digital microscope can be used for a range of applications from schools to pathology labs. The Chrono's microscopes also benefit from having low minimum computer requirements.
- System Requirements
- OS: Windows XP SP2/Vista , Vista SP1/W 7, Windows 8
- CPU: Pentium IV 1.0G, Celeron, AMD Athlon
- CD-ROM
- Available USB 2.0 port
- 256MB RAM
- 100MB available hard disk space
- Graphic card: 16-bit