

Project..... Comments.....

Fixture Type..... Prepared By.....

Product Description:

High power Sharp LED. Short Form - same size as a GU10 Halogen lamp. High colour rendering index (Ra) >83. Dimmable with most UK and European dimmers. 40 degree beam angle. Average lifetime up to 30,000 hours. 2 Year guarantee.

Product Image & Dimensions:



Overall Diameter	50 mm
Overall Length	55 mm
Overall Height	55 mm

Product Specifications:

- Lamp Type: GU10
- Lamp Base: GU10
- Input Voltage (Min): 220 V
- Input Voltage (Max): 240 V
- Dimmable: Yes
- Beam Angle: 40 °
- Lifespan: 30000 hrs
- Overall Diameter: 50 mm
- Overall Length: 55 mm
- Overall Height: 55 mm
- Guarantee: 2 Years

Compliance & Approvals:



SKU Table and Ordering:

SKU Code	Wattage	Colour Temperature	Lumens	Candelas	Colour	EAN	Qty
AU-DGU1060W/30	6 W	3000 K	280 lm	480 cd	White	5055155484293	<input type="text"/>
AU-DGU1060W/40	6 W	4000 K	300 lm	515 cd	White	5055155484309	<input type="text"/>

Warranty:

For available warranty information for this product, please visit:

<http://gb.auroralighting.com/Products/Lamps/Economy-LED-Lamps/240V-GU10/220-240V-GU10-6W-White-dimmable-LED-Lamp.aspx>

UK Sales

16 Alban Park
Hatfield Road, St. Albans
United Kingdom
PH: +44 (0) 1727 83 66 11
FX: +44 (0) 1727 83 66 22

UK Distribution

Apex Park, 6 Little Burrows
Burrowfields, Welwyn Garden City
AL7 4SW
United Kingdom
PH: +44 (0) 1707 35 18 20
FX: +44 (0) 1727 35 18 21