

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [50-57-9305](#)  
**Status:** **Active**  
**Overview:** [SL™ Modular Connectors](#)  
**Description:** [SL™ Crimp Housing, Single Row, Version D, Back Ribs, 5 Circuits](#)



Series

image - Reference only

**Documents:**

- |                                                      |                                                      |
|------------------------------------------------------|------------------------------------------------------|
| <a href="#">3D Model</a>                             | <a href="#">Product Specification PS-71851 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                        | <a href="#">Test Summary TS-70058-001 (PDF)</a>      |
| <a href="#">Product Specification PS-70058 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">Product Specification PS-70400 (PDF)</a> |                                                      |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                                        |
|----------------|----------------------------------------|
| Product Family | Crimp Housings                         |
| Series         | <a href="#">70066</a>                  |
| Application    | Signal, Wire-to-Board                  |
| Comments       | Version D                              |
| Overview       | <a href="#">SL™ Modular Connectors</a> |
| Product Name   | SL™                                    |
| UPC            | 800753578074                           |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Circuits (maximum)            | 5               |
| Color - Resin                 | Black           |
| Flammability                  | 94V-0           |
| Gender                        | Female          |
| Glow-Wire Compliant           | No              |
| Keying to Mating Part         | Yes             |
| Lock to Mating Part           | No              |
| Material - Resin              | Polyester Alloy |
| Net Weight                    | 0.037/g         |
| Number of Rows                | 1               |
| Packaging Type                | Bag             |
| Panel Mount                   | No              |
| Pitch - Mating Interface      | 2.54mm          |
| Stackable                     | Yes             |
| Temperature Range - Operating | -40°C to +105°C |

**Electrical**

|                               |    |
|-------------------------------|----|
| Current - Maximum per Contact | 3A |
|-------------------------------|----|

**Material Info**

|                 |            |
|-----------------|------------|
| Old Part Number | 70066-0109 |
|-----------------|------------|

**Reference - Drawing Numbers**

|                       |                              |
|-----------------------|------------------------------|
| Product Specification | PS-70058, PS-70400, PS-71851 |
| Sales Drawing         | SD-70066-0106-0129           |
| Test Summary          | TS-70058-001                 |

**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC**  
**Contains SVHC: No**  
**Low-Halogen Status**  
**Not Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**

[70066Series](#)

**Mates With**

[70004 Interim Clip](#), [70013](#), [70022](#), [70104](#),  
[70475](#), [70431](#), [70543](#), [70553](#)

**Use With**

SL™ Crimp Terminal [70021](#), [70058](#), [71851](#)