





1	A	B	C	D	E	F	G	H																																																																																																																														
1																																																																																																																																						
2	Pos.	Stk./ pcs	Bezeichnung/ Description	Typ-Nr./ Type-No.	Bemerkung/ Remark	Pos.	Stk. pcs	Kabel cable	Kunden Art.-Nr. customer part-no.	Kabeltyp cable type	Art.Nr. IMS Part.No. IMS	Zuschnittsl. I cut length I	Gesamtlänge L total length L																																																																																																																									
	①	1	Kabelstecker Cable mount plug	3796.91.1410.023 (1073712)		③	1	K-2084-01	-	RG 316 U	(1124698)	44,9±1	60±2																																																																																																																									
	②	1	Kabelstecker Cable mount plug	526.42.1410.021 (1071645)	Laenge / Length		1	K-2084-02	-	Enviroflex 316	(1128687)	84,9±1	100±2																																																																																																																									
	③	1	Kabel Cable	siehe Tabelle rechts! see chart on the right side!			1	K-2084-03	-	Enviroflex 316	(1128687)	234,9±1	250±2																																																																																																																									
	④	1	Schrumpfschlauch *) Heat shrink tube	1/8-0 (1125987)	20±2		1	K-2084-04	-	Enviroflex 316	(1128687)	484,9± 1	500± 2																																																																																																																									
	⑤	1	Schrumpfschlauch *) Heat shrink tube	1/8-0 (1125987)	20±2		1	K-2084-05	-	Enviroflex 316	(1128687)	984,9±1	1000±2																																																																																																																									
	⑥																																																																																																																																					
	⑦																																																																																																																																					
3	Anzahl der Kabel / No. of cable		Stueck / Pcs.																																																																																																																																			
	Kabelzuschnitt / Stripping dimension		Kabelzuschnitt / Stripping dimension		Bemerkungen / Remarks																																																																																																																																	
	POS. ①		POS. ②		Pos. 1 Aussen/outer : crimp  SW 3.25 Innen/inner : loeten / solder																																																																																																																																	
					Pos. 2 Aussen/outer : crimp  SW 3.25 Innen/inner : loeten / solder																																																																																																																																	
4					Pruefspannung: 500Veff/50Hz Test-voltage : 500Veff/50Hz																																																																																																																																	
5																																																																																																																																						
	Referenzebene Reference plane																																																																																																																																					
6																																																																																																																																						
	A	B	C	D	E	F	G	H																																																																																																																														
					<table><tr><td colspan="5"></td><td colspan="2">general tolerance ISO 2768 mH</td><td colspan="2">----- AA-CS-12</td><td colspan="2">scale: 1:1</td></tr><tr><td colspan="5"></td><td colspan="2">date</td><td colspan="2">name</td><td colspan="4" rowspan="3">HF-Leitung Flexibel RF-flexible Cable Assembly</td></tr><tr><td colspan="5"></td><td colspan="2">30.11.04</td><td colspan="2">Zech</td></tr><tr><td colspan="5"></td><td colspan="2">checked</td><td colspan="2"></td></tr><tr><td colspan="5"></td><td colspan="2">Norm</td><td colspan="2"></td><td colspan="4" rowspan="3">K-2084-XX</td></tr><tr><td colspan="5"></td><td colspan="2">044571</td><td colspan="2"></td></tr><tr><td colspan="5"></td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="5">EC_085_08</td><td>c</td><td>Length modified</td><td>29.04.08</td><td>Sarfe</td><td colspan="2"></td><td colspan="2" rowspan="3">Rev. c</td></tr><tr><td colspan="5">design</td><td>b</td><td>add. cables</td><td>12.03.07</td><td>Zech</td><td colspan="2"></td></tr><tr><td colspan="5">design</td><td>a</td><td>Pos.1-Zuschnitt</td><td>03.05.06</td><td>Zech</td><td colspan="2"></td></tr><tr><td colspan="5">nr.</td><td>rev.</td><td>alteration</td><td>date</td><td>name</td><td colspan="2"></td><td colspan="2"></td></tr></table>														general tolerance ISO 2768 mH		----- AA-CS-12		scale: 1:1							date		name		HF-Leitung Flexibel RF-flexible Cable Assembly									30.11.04		Zech							checked									Norm				K-2084-XX									044571													EC_085_08					c	Length modified	29.04.08	Sarfe			Rev. c		design					b	add. cables	12.03.07	Zech			design					a	Pos.1-Zuschnitt	03.05.06	Zech			nr.					rev.	alteration	date	name				
					general tolerance ISO 2768 mH		----- AA-CS-12		scale: 1:1																																																																																																																													
					date		name		HF-Leitung Flexibel RF-flexible Cable Assembly																																																																																																																													
					30.11.04		Zech																																																																																																																															
					checked																																																																																																																																	
					Norm				K-2084-XX																																																																																																																													
					044571																																																																																																																																	
EC_085_08					c	Length modified	29.04.08	Sarfe			Rev. c																																																																																																																											
design					b	add. cables	12.03.07	Zech																																																																																																																														
design					a	Pos.1-Zuschnitt	03.05.06	Zech																																																																																																																														
nr.					rev.	alteration	date	name																																																																																																																														