

RS Part Number: **773-8024**
 Specifications and dimensions



- Boxed isolator 4 pole
- Metal enclosure with padlockable handle
- Epoxy coated steel construction

Specifications	
Height	220 mm
Width	145 mm
Depth	90 mm
Depth including switch	134 mm
Degree of protection	IP54
Colour of base	RAL7043
Colour of Lid	RAL7032
Rated operational current Ie AC21A	40 A
Rated operational current Ie AC22A	32 A
Rated operational voltage Ue IEC & EN	690 V
Rated operational power AC23A 380-440V	18.5 kW
Rated operational power AC3 440V	11 kW
Maximum gL fuse size IEC	32 A
Rated fused short circuit capacity IEC	30 kA
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	6 mm ²
Recommended tightening torque	1.7 Nm
Number of possible auxilliary contacts	1
Related products	
Neutral contact (early make/late break)	136-5280