



Main

Commercial Status	Commercialised
Range	Spacial S24
Device application	Safety and alarm system
Product or component type	Industrial box
Height	182 mm
Width	132 mm
Depth	107 mm
Internal height	180 mm
Internal width	130 mm
Internal depth	96 mm
Enclosure mounting	Surface
Device composition	M6 x 8 grounding screw 4 x nut
Type of front cover	Door with window thickness 3 mm
Lock type	Side : 3 mm double bar insert

Complementary

Material	Steel
Surface finish	Epoxy-polyester powder
Colour	Red (RAL 3000)
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK07
Environmental characteristic	UV resistant Corrosion resistance

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.