

## Datasheet

# RS Pro Insulated Crimp Spade Connector, 1.5mm<sup>2</sup> to 2.5mm<sup>2</sup>, 16AWG to 14AWG, M3 Stud Size, Blue Vinyl

RS Stock No: **149-524**



## Product Details

RS Pro insulated crimp spade connector in blue vinyl colour, has 1.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup>, 16 to 14 AWG wire size and M3 stud size. This connector has a PVC funnel entry range of crimps on reels. It is available in a variety of the most popular sizes.

## Features and Benefits

- PVC funnel entry range of crimps on reels
- Available in a variety of the most popular sizes
- Red 0.5 to 1.5 mm<sup>2</sup>, blue 1.5 to 2.5 mm<sup>2</sup> and yellow 4 to 6 mm<sup>2</sup>

**Specifications:**

Colour	Blue
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	Vinyl
Maximum Wire Size (AWG)	14 AWG
Maximum Wire Size (mm <sup>2</sup> )	2.5 mm <sup>2</sup>
Minimum Wire Size (AWG)	16 AWG
Minimum Wire Size (mm <sup>2</sup> )	1.5 mm <sup>2</sup>
Overall Length	19.5 mm
Stud Size	M3.2
Thickness	0.8 mm
Width	6 mm
Wire Size	16 to 14 AWG
Current Rating	27 A
Temperature Rating	+75°C
Type	Flared Vinyl without Copper Sleeve
Voltage Rating	600 V