

HDM401HIHSUVH4



Article Number: 151-07300

Medium Torque Mount, Mounting Hole .375", Max Torque 40.0 lb - ft, PA66HIRHSUV, Black, 500/pkg

 RoHS

Base Data

Local Order Number	HDM401HIHSUVH4
Type	HDM401
Color	Black (BK)
Features and Benefits	• Mount and tie combination makes it easy to service bundles in the field. • Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments. • Eliminates the needs for multiple sized fix diameter clamps.
Product Description	This heavy duty mount, when used with a cable tie eliminates the need to carry multiple sizes of fixed bundle diameter clamps; which reduces inventory and purchasing costs while simplifying the assembly process.
Fixation Method (FF)	Screw Mounting and Rivet
Short Description	Medium Torque Mount, Mounting Hole .375", Max Torque 40.0 lb - ft, PA66HIRHSUV, Black, 500/pkg

Product Dimensions

Length L (imperial)	1.8 "
Length L (metric)	46.0 mm
Width W (imperial)	0.96 "
Width W (metric)	24.0 mm
Cable Tie Width Max (imperial)	0.5 "
Cable Tie Width max. (metric)	12.7 mm
Mounting Hole Diameter D (imperial)	0.375 "
Mounting Hole Diameter D (metric)	9.5 mm

Logistics and Packaging

Quantity per	bag
Package Quantity	500
Carton Quantity	500

Material and Specifications

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL94 HB
Maximum Torque (kgf-cm)	553 kgf-cm
Maximum Torque (lbf-ft)	40 lbf-ft
Operating Temperature	-40 °F to +230 °F (-40 °C to +110 °C)
ROHS Conformity	Yes

