

Plastic label - UC-EMLP (20X8) - 0819327

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Plastic label, Sheet, white, Unlabeled, Can be labeled with: Bluemark, Plotter, BLUEMARK CLED, Mounting type: Adhesive, Lettering field: 20 mm x 8 mm



Why buy this product

- The UC-EMLP ... UniCard labeling range includes self-adhesive device markers with good adhesive properties
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy

Key commercial data

Packing unit	0
Minimum order quantity	10
Catalog page	Page 196 (CL2-2011)
GTIN	 4 046356 152464
Custom tariff number	39269097
Country of origin	GERMANY

Technical data

General

Length (b)	20 mm
Width (a)	8 mm
Color	white
Inflammability class according to UL 94	V2
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C
Components	free from silicone and halogen
Material	PA
Number of individual labels	10
Number of individual labels per row	2

Plastic label - UC-EMLP (20X8) - 0819327

Classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410
UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

Accessories

Accessories

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER, for accommodating UC-EMP..., UC-EMLP...