

# Product Information



## AA20POI050B10-11x20

EAN 4031582317503

Swivel castor, housing made of Polypropylene, stem with circlip.

Wheel centre made of Polypropylene, plain bearing

Technical Data	
Wheel diameter	50 mm
Width of Tread	8 mm
Castor width	55 mm
Metal stem with circlip	11 x 20 mm
Swivel Interference	98 mm
Overall height	58 mm
Temperature	- 10 / + 40 °C
Weight	0.095 kg
Swivel Radius	49 mm
Hardness of tread	D 65 Shore



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

# Product Information



## AA20POI050B10-11x20

EAN 4031582317503

