

Datasheet

5m Flexible Reinforced Ducting

RS Stock number [413-8985](#)



Description:

A PVC coated steel spiral helix embedded between two layers of thermoplastic, heat resistant alcryn rubber.

Application:

This ducting is ideally suited for automotive air intakes, general purpose air and fume extraction. It also has excellent resistance to acid fumes and oil fumes. It has outstanding resistance to ozone, sunlight, ageing, oxidation together with good low and high temperature resistance. It also has good resistance to fatigue and vibration.

Advantages:

High temperature resistance. Smooth bore.

Specification:

- Bend Radius: 120mm
- Colour: Black
- Inner Diameter: 120mm
- Length: 5m
- Material: Rubber
- Outer Diameter: 127mm
- Reinforced: Yes
- Suitable: Applications Air, Gas
- Temperature: -25°C +125°C