

LLL185R71E103MA01#

" # " indicates a package specification code.



< List of part numbers with package codes >
 LLL185R71E103MA01L , LLL185R71E103MA01K

Shape

L size	0.8 ± 0.1mm
W size	1.6 ± 0.1mm
T size	0.5 ± 0.1mm
External terminal width e	0.25 ± 0.15mm
Distance between external terminals g	0.1mm min.
Size code in inch(mm)	0306 (0816)

References

Packaging	Specifications	Minimum quantity
L	180mm Embossed taping	4000
K	330mm Embossed taping	10000

Mass (typ.)	
1 piece	3.9mg
180mm Reel	100g


Specifications

Capacitance	10000pF ± 20%
Rated voltage	25Vdc
Temperature characteristics (complied standard)	X7R(EIA)
Capacitance change rate	± 15.0%
Temperature range of temperature characteristics	-55 to 125
Operating temperature range	-55 to 125


⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


▪ Frequency characteristics (ESR, Impedance)




▪ S parameter (Smith chart S11)



▪ DC bias characteristics



▪ AC voltage characteristics



▪ Capacitance - temperature characteristics

