

Datasheet

Art.No. 91.932.3053.0

Male connector with strain relief GST15i3S S1 ZR1W WS

Connector GST15i3, 3 pole, male, screw connection, 250V/16A, color of coding: white, color of housing: white



Art.No.	91.932.3053.0
EAN	4015573833838
Order unit	1 pieces

Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	White
Marking of poles	L, N, PE
Color of housing inclusive strain relief	White

Connection Data

Cable diameter	9 mm
Cable diameter 2	5.5 mm
Connection cross section solid	1.5 mm ²
Cross section solid 2	0.5 mm ²
Connection cross section stranded	1.5 mm ²
Cross section stranded 2	0.5 mm ²
Terminations per pole	1

Model

Model	male
Number of poles	3

Connection type	Screw connection
Degree of protection (IP)	IP20

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	53.2 mm
Width	23 mm
Height	13.8 mm

Drawings

