

Insert strip - ESL 62X10 YE - 0821195

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Insert strip, Sheet, yellow, unlabeled, can be labeled with: Office printing systems, Plotter, Mounting type: Insert, Lettering field: 62 x 10 mm




The figure shows the ESL 62X64, in white

Why buy this product

- Insert labels for plastic cable markers
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking".



Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 046356 329453
Weight per Piece (excluding packing)	17.11 g
Custom tariff number	39206219
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	62 mm
Width (a)	10 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Note	Print image may vary depending on laser printer
Color	yellow
Components	free from silicone and halogen
Material	Polyester foil

Insert strip - ESL 62X10 YE - 0821195

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	72
Number of individual labels per row	3
Marking mounting type	Insert

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410