

Cable - FLK 50-PA/EZ-DR/HF/KS/1500/YOC - 2904995

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled halogen-free round cable with two molded 50-pos. socket strips (bridged contacts). The cable is suitable for the SDV 531 card; cable length: 15.0 m

Illustration shows the product FLK 50-PA/EZ-DR/KS/ 200/YUC



Key commercial data

Packing unit	1
GTIN	 4 046356 906777
Custom tariff number	85444290

Technical data

General

Nominal voltage U_N	30 V DC
Max. current carrying capacity per path	500 mA (Up to 55°C ambient temperature)
Max. conductor resistance	0.16 Ω /m
Length of cable	15 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	11 mm
Shielding	yes
Standards/specifications	Halogen-free sheath IEC 60754-1
Outer sheath, material	PVC
External sheath, color	Gray RAL 7035

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-3

Cable - FLK 50-PA/EZ-DR/HF/KS/1500/YOC - 2904995

Technical data

Environmental conditions

Resistance to oil	DIN VDE 0472 Part 803, test type B
Gasoline resistance	Against occasional splashes

Connector, module side

Number of positions	50
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	1

Connector, controller side

Number of positions	50
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	1

Connection data

Connection method	Screw connection
Torque	0.5 Nm

Classifications

eCl@ss

eCl@ss 4.1	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 8.0	27249205

ETIM

ETIM 4.0	EC000237
ETIM 5.0	EC000237

Accessories

Spare parts

Screw set - VF-SCREW-YOKOGAWA/M3X18/DCS - 2902873



Replacement screw M3x18 for Yokogawa system cable, front adapter control side.

Cable - FLK 50-PA/EZ-DR/HF/KS/1500/YOC - 2904995

Accessories

Screw set - VF-SCREW-YOKOGAWA/M4X25/KS - 2902874



Replacement screw M4x25 for Yokogawa system cable, module side.

Drawings

Connection diagram

50-pos. connector to the I/O card	50-pos. connector to the module	Wire color
1	50	black
2	49	brown
3	48	red
4	47	orange
5	46	yellow
6	45	green
7	44	blue
8	43	violet
9	42	gray
10	41	white
11	40	white-black
12	39	white-brown
13	38	white-red
14	37	white-orange
15	36	white-yellow
16	35	white-green
17	34	white-blue
18	33	white-violet
19	32	white-gray
20	31	brown-black
21	30	brown-red
22	29	brown-orange
23	28	brown-yellow
24	27	brown-green
25	26	brown-blue
26	25	brown-violet
27	24	brown-gray
28	23	brown-white
29	22	green-black
30	21	green-brown
31	20	green-red
32	19	green-orange
33	18	green-blue
34	17	green-violet
35	16	green-gray
36	15	green-white
37	14	yellow-black
38	13	yellow-brown
39	12	yellow-red
40	11	yellow-orange
41	10	yellow-blue
42	9	yellow-violet
43	8	yellow-gray
44	7	yellow-white
45	6	gray-black
46	5	gray-brown
47	4	gray-red
48	3	gray-orange
49	2	gray-yellow
50	1	gray-green